



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
DIA: 0.000 MM
SPOT DIAGRAM

47650
TUE DEC 16 2008 UNITS ARE μm .
FIELD : :
RMS RADIUS : 3.720
GD RADIUS : 6.720
SCALE BAR : 20



REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47650
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 1184.6248 μm
DIFFRACTION LIMITED RANGE: 601.633 μm
PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

47650
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47650
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com