



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



TECHSPEC® ACHROMATIC LENSES



SPOT DIAGRAM
49357INK
TUE DEC 16 2008 UNITS ARE μm.
FIELD : 1
RMS RADIUS : 24.496
GD RADIUS : 68.357
SCALE BAR : 200
REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
49357INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 445.8882 μm
DIFFRACTION LIMITED RANGE: 13.188 μm
PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT
EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT
49357INK
TUE DEC 16 2008
MAXIMUM SCALE: ± 500.000 μm.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM
49357INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm.
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF
EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com