




NOTES:

1. SUBSTRATE: SCHOTT RG610
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CUT-ON WAVELENGTH (nm)	610 ±6
PASSBAND LIMIT 1 (nm)	690
STOPBAND LIMIT (nm)	530
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED

EO® Edmund Optics®



THIRD ANGLE
PROJECTION

TITLE

SCHOTT RG610 50 x 50mm COLORED
LONGPASS FILTER, 3mm THK

ALL DIMS IN

mm

DWG NO

14513

SHEET
1 OF 1