





NOTES:

1. SUBSTRATE: Hoya IR85N



LONGPASS FILTER


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	<60
TH (%)	N/A
CUT-ON WAVELENGTH (nm)	850±10
SURFACE QUALITY	60-40
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED



THIRD ANGLE
PROJECTION



TITLE

Hoya IR85N (850nm), 50.8mm Sq., 2.5mm
Thick, Colored Glass Longpass Filter

ALL DIMS IN

mm

DWG NO

18910

SHEET
1 OF 1