


NOTES:


- 1. SUBSTRATE:
TAC FILM
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
- 3. PROTECTIVE FILM ON NON-MATTE SURFACE SHOULD BE REMOVED BEFORE USE
- 4. WAVELENGTH RANGE: 300 - 1100 nm
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

| | | | | |
|--------------------------------------------------------------------------------------------------------------|----|--------|----------------------------------|-----------------|
| THIRD ANGLE PROJECTION  | | TITLE | 150 x 150mm Light Diffusing Film | |
| ALL DIMS IN | mm | DWG NO | 20219 | SHEET 1 OF 1 |